



YGA6C2NTN Comp Ground Lug, 6 AWG Cu, 2-Hole NEMA Pad, Tinned

By Burndy
Catalog # [YGA6C2NTN](#)



HYLUG™ Copper Compression Terminal for Grounding; 2-Hole

Features

- Irreversible compression ground terminal specifically designed for grounding applications
- Each connector has an inspection probe hole to ensure proper cable insertion
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- UL486A Listed
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	6 AWG
Conductor - Copper Str Size	6 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.83 in
Dimension - Bolt Hole Size inch	0.52 in
Package Height	0.000 in

Dimension - B Length fraction	1 in
Package Weight	0.000 lb.
Dimension - Width inch	0.41 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	112 mm
Dimension - B Length inch	1.09 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Width fraction	2/5 in
Dimension - N inch	0.62 in
Dimension - Hole Size mm	14 mm
Dimension - Bolt Size inch	0.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.40 in
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size inch	1/2

General

Plated	Y
Color Code	Blue
Trade Name	HYLUG™
Die Index	• 7 • 374
UPC	781810359235
Type	Terminals
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810359235
UPC 14 Digit GTIN	00781810359235

Logistics

Minimum Pack Quantity	1
Pallet Quantity	24000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)