



YGA8CTC14 Comp Ground Lug, #8 AWG Cu, 1-Hole, 1/4" Stud

By Burndy
Catalog # [YGA8CTC14](#)



HYLUG™ Copper Compression Terminal for Grounding; 1-Hole

Features

- Irreversible compression ground terminal specifically designed for grounding applications
- Each connector has an inspection probe hole to ensure proper cable insertion
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- UL486A Listed
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	• UL467 • UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	8 Sol./8 Str.
Conductor - Copper Solid Size	8
Conductor - Copper Solid Size Range	8
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	8 Sol / 8 AWG

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	0.44 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	43 mm
Dimension - Outside Diameter inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.27 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.27 in
Dimension - B Length fraction	4/5 in
Dimension - B Length inch	0.81 in
Dimension - N inch	0.31 in
Dimension - Bolt Size inch	0.25 in
Dimension - Length Overall inch	1.69 in

General

Trade Name	HYLUG™
Die Index	49
Plated	N
Color Code	Red
UPC	781810102442
Type	Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810102442
UPC 14 Digit GTIN	00781810102442

Logistics

Minimum Pack Quantity	1
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)