



YGC6C8 Compression C-Crimp Connector, #6 AWG Run, #8 AWG Tap

By Burndy
Catalog # [YGC6C8](#)

Copper Compression C Tap, 6 AWG(Run)/8 AWG(Tap)



Features

- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ E2 oxide inhibiting compound

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	6 AWG
Conductor - Copper Str Run	6 AWG
Conductor - Copper Solid Run Range	6 AWG
Conductor - Copper Solid Run	6 AWG
Conductor - Copper Solid Tap Range	8 AWG
Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Str Tap Range	8 AWG
Conductor - Copper Str Tap	8 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	18.5 mm
Dimension - Height inch	0.73 in
Dimension - Height fraction	46/63 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	16 mm
Dimension - Length Overall inch	0.62 in

General

Plated	N
Trade Name	CRIMPIT™
Die Index	BG
UPC	781810102596
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810102596
UPC 14 Digit GTIN	00781810102596

Logistics

Minimum Pack Quantity	1
Pallet Quantity	46400
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand