



YGC8C8 Comp C-Crimp, #8 Sol/Str Run, #8 Sol/Str Tap

By Burndy
Catalog # [YGC8C8](#)

COPPER CRIMPIT™ Compression C Connector, #8 Sol/Str Run, #8 Sol/Str Tap



Features

- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ E2 oxide inhibiting compound

Application

For Direct Burial In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	8 AWG
Conductor - Copper Str Run	8 AWG
Conductor - Copper Solid Run Range	8 AWG
Conductor - Copper Solid Run	8 AWG
Conductor - Copper Solid Tap Range	8 AWG
Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Str Tap Range	8 AWG
Conductor - Copper Str Tap	8 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
--	---

Connector Type	Tap
----------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	11.7 mm
Dimension - Height inch	0.46 in
Dimension - Height fraction	23/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	13 mm
Dimension - Length Overall inch	0.52 in

General

Product Family	Grounding and Bonding Connectors>"Hygground" Compression Grounding Connectors>C-Taps
Trade Name	CRIMPIT™
Die Index	162
Plated	No
Sub Brand	HYGGROUND, CRIMPIT
Product Type	Compression
UPC	781810102558
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810102558
UPC 14 Digit GTIN	00781810102558

Logistics

Minimum Pack Quantity	1
Pallet Quantity	46400
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)