



YGHA282NU Compression Grounding Lug, 4/0 AWG Cu, Undrilled

By Burndy
Catalog # [YGHA282NU](#)



Undrilled Heavy Duty Irreversible Compression Terminals.

Features

- Irreversible compression ground terminal specifically designed for grounding applications
- Each connector has an inspection probe hole to ensure proper cable insertion
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- UL486A Listed
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • UL468A-468B • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.22 in
Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-9/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	125 mm
Dimension - B Length inch	1.18 in
Dimension - Outside Diameter inch	0.89 in
Dimension - D inch	3.00 in
Dimension - Length Overall inch	4.94 in

General

Plated	N
Trade Name	HYLUG™
Die Index	17
UPC	781810277126
Type	Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810277126
UPC 14 Digit GTIN	00781810277126

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)