



YGHA28N Comp Ground Lug, 4/0 AWG Cu, 1-Hole, 1/2" Stud

By Burndy
Catalog # [YGHA28N](#)



HYLUG™ Copper Compression Terminal for Grounding; Heavy
Duty; 1-Hole

Features

- Irreversible compression ground terminal specifically designed for grounding applications
- Each connector has an inspection probe hole to ensure proper cable insertion
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- UL486A Listed
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • UL468A-468B • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.22 in
----------------------------	---------

Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-9/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.64 in
Dimension - L Length Overall mm	81 mm
Dimension - B Length inch	1.18 in
Dimension - Outside Diameter inch	0.89 in
Dimension - D inch	1.27 in
Dimension - N inch	0.63 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	3.18 in

General

Plated	N
Trade Name	HYLUG™
Die Index	17
UPC	781810158388
Type	Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810158388
UPC 14 Digit GTIN	00781810158388

Logistics

Minimum Pack Quantity	10
Pallet Quantity	5760
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)