



YGHA2C2NNP Comp Ground Lug, 2 AWG Cu, 2-Hole NEMA

By Burndy
Catalog # [YGHA2C2NNP](#)

Copper Compression Lug, Heavy Duty, 2 Hole with Inspection probe hole, 2 AWG, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel without oxide inhibitor



Features

- Irreversible compression ground terminal specifically designed for grounding applications
- Each connector has an inspection probe hole to ensure proper cable insertion
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- UL486A Listed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • UL 486A-486B • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • UL 486A-486B • IEEE 837
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Str Size	2 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.97 in
Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.63 in
Dimension - L Length Overall mm	107 mm
Dimension - B Length inch	0.75 in
Dimension - Outside Diameter inch	0.50 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.21 in

General

Plated	N
Trade Name	HYLUG™
Die Index	11
UPC	781810198278
Type	Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810198278
UPC 14 Digit GTIN	00781810198278

Logistics

Minimum Pack Quantity	25
Pallet Quantity	9800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)