



YGHA2CNTN Comp Ground Lug, 2 AWG Cu, 1-Hole, 1/2", Tinned

By Burndy
Catalog # [YGHA2CNTN](#)



Tin Plated Heavy Duty Irreversible Compression Terminals

Features

- Irreversible compression ground terminal specifically designed for grounding applications
- Each connector has an inspection probe hole to ensure proper cable insertion
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- UL486A Listed
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Standards - Industry Standards Met	• UL467 • UL468A-468B • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size A	2 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	2 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	0.97 in
----------------------------	---------

Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.64 in
Dimension - B Length inch	0.75 in
Dimension - Outside Diameter inch	0.50 in
Dimension - D inch	1.27 in
Dimension - N inch	0.63 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	2.46 in

General

Plated	Y
Trade Name	HYLUG™
Die Index - Element B	11
UPC	621945454743
Type	Terminals
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	621945454743
UPC 14 Digit GTIN	00621945454743

Logistics

Minimum Pack Quantity	1
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)