



**YGHC26C26 C-Tap, Run: 1-2/0 Str, 3/8" Rod,  
Tap: 1-2/0 Str**

By Burndy  
Catalog # [YGHC26C26](#)



Copper Compression C Connector, 1 - 2/0 AWG(Str), 3/8" Rod (Run) & 1 - 2/0 AWG(Str) (Tap)

**Features**

- Irreversible compression ground tap figure C connector
- C-shaped opening permits placing two continuous parallel cables into conductor groove
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

**Application**

For Direct Burial Cables

**Specifications**

|                                         |                                                                                                  |
|-----------------------------------------|--------------------------------------------------------------------------------------------------|
| Certification - UL Recognized           | No                                                                                               |
| Buy American Compliant                  | No                                                                                               |
| Certification - cULus                   | No                                                                                               |
| Buy America(n) Qualified                | BABA Compliant (All status valid till December 2026)                                             |
| Industry Standard(s)                    | Direct Burial                                                                                    |
| Certification - ETL                     | No                                                                                               |
| Standards - Industry Standards Met      | <ul style="list-style-type: none"><li>• UL467</li><li>• IEEE 837</li><li>• UL468A-468B</li></ul> |
| Standards - RoHS Compliance             | CM                                                                                               |
| Status                                  |                                                                                                  |
| Certification - UL Listed Direct Burial | Yes                                                                                              |
| UL Listed                               | Yes                                                                                              |
| Certification - CSA Approved            | Yes                                                                                              |

**Conductor**

|                                  |                                                                                         |
|----------------------------------|-----------------------------------------------------------------------------------------|
| Conductor - Rod Run Range        | 3/8 in                                                                                  |
| Conductor - Rod Run              | 3/8 in                                                                                  |
| Conductor - Copper Str Run Range | 1 AWG-2/0 AWG                                                                           |
| Conductor - Copper Str Run       | <ul style="list-style-type: none"><li>• 1 AWG</li><li>• 1/0</li><li>• 2/0 AWG</li></ul> |
| Conductor - Copper Str Tap Range | 1 AWG-2/0 AWG                                                                           |
| Conductor - Copper Str Tap       | <ul style="list-style-type: none"><li>• 1 AWG</li><li>• 1/0</li><li>• 2/0 AWG</li></ul> |

**Configuration**

|                                |     |
|--------------------------------|-----|
| Physical Attribute - Number of | 1   |
| Crimps Required                |     |
| Connector Type                 | Tap |

**Dimensions**

|                                 |            |
|---------------------------------|------------|
| Package Height                  | 0.000 in   |
| Dimension - Height mm           | 39.1 mm    |
| Dimension - Height inch         | 1.54 in    |
| Dimension - Height fraction     | 1-27/50 in |
| Package Weight                  | 0.000 lb.  |
| Package Length                  | 0.000 in   |
| Package Width                   | 0.000 in   |
| Dimension - L Length Overall mm | 19 mm      |
| Dimension - B Length inch       | 0.75 in    |
| Dimension - Length Overall inch | 0.75 in    |

**General**

|                   |                                                                                     |
|-------------------|-------------------------------------------------------------------------------------|
| Product Family    | Grounding and Bonding Connectors>"Hyground" Compression Grounding Connectors>C-Taps |
| Trade Name        | HYTAP™                                                                              |
| Die Index         | O                                                                                   |
| Plated            | No                                                                                  |
| Sub Brand         | HYGROUND, HYTAP                                                                     |
| Product Type      | Compression                                                                         |
| UPC               | 781810221037                                                                        |
| Type              | Taps                                                                                |
| Material          | Copper                                                                              |
| Plating Type      | Unplated                                                                            |
| UPC 12 Digit      | 781810221037                                                                        |
| UPC 14 Digit GTIN | 00781810221037                                                                      |

**Logistics**

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 1     |
| Pallet Quantity       | 14800 |
| Carton Quantity       | 50    |

**Product Assets**

[Catalog \[English\]](#)