



YGHC26C2TN Compression Grounding C-TAP Connector

By Burndy
Catalog # [YGHC26C2TN](#)

Copper Compression Ground Connector; .75 IN L; 1-2/0 Str. (Run); #6 Sol.-#2 Str. (Tap)



Features

- Irreversible compression ground tap figure C connector
- C-shaped opening permits placing two continuous parallel cables into conductor groove
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

- 6 AWG
- 5 AWG
- 4 AWG
- 3 AWG
- 2 AWG

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • IEEE 837 • UL468A-468B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	Direct Burial
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Rod Run Range	3/8 in
Conductor - Rod Run	3/8 in
Conductor - Copper Str Run Range	1 AWG-2/0 AWG
Conductor - Copper Str Run	• 1 AWG • 1/0 • 2/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-1 AWG
Conductor - Copper Solid Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - Copper Str Tap Range	7 AWG-2 AWG
Conductor - Copper Str Tap	• 7 AWG

Configuration

Physical Attribute - Number of	1
Crimps Required	
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	35.8 mm
Dimension - Height inch	1.41 in
Dimension - Height fraction	1-25/61 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.75 in

General

Plated	Y
Trade Name	HYTAP™
Die Index	O
UPC	781810167298
Type	Taps
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810167298
UPC 14 Digit GTIN	00781810167298

Logistics

Minimum Pack Quantity	1
Pallet Quantity	14800
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)



A Hubbell brand