



YGHC29C29NP Compression Grounding C-TAP Connector

By Burndy
Catalog # [YGHC29C29NP](#)

Copper Compression Ground Connector; 2/0 Str.-250 kcmil (Run & Tap); 997 Index, NO Penetrox™

Features

- Irreversible compression ground tap figure C connector
- C-shaped opening permits placing two continuous parallel cables into conductor groove
- UL467 Listed
- Acceptable for direct burial in earth or concrete

Specifications

Certification - ETL	No
Standards - Industry Standards Met	• UL467 • IEEE 837 • UL468A-468B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL Listed to UL 467 • CSA Certified to C22.2 No.41
UL Listed	No
Certification - CSA Approved	No

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	997 mm

General

Plated	N
Trade Name	HYTAP™
UPC	781810568903
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810568903
UPC 14 Digit GTIN	00781810568903

Logistics

Minimum Pack Quantity	1
Pallet Quantity	6125
Carton Quantity	125

Product Assets

[Catalog \[English\]](#)