



YGHC29C29TN Compression Grounding C-TAP Connector

By Burndy
Catalog # [YGHC29C29TN](#)

Copper Compression C Connector, 2/0 AWG(Str) - 250 kcmil, 1/2" or 5/8" Rod (Run) & 2/0 AWG(Str) - 250 kcmil (Tap), Tin Plated



Features

- Irreversible compression ground tap figure C connector
- C-shaped opening permits placing two continuous parallel cables into conductor groove
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

- 4/0 AWG
- 250 kcmil

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • IEEE 837 • UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	• UL467 • IEEE 837 • UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Rod Run Range	1/2 in-5/8 in
Conductor - Rod Run	• 1/2 in • 5/8 in
Conductor - Copper Str Run Range	2/0 AWG-250 kcmil
Conductor - Copper Str Run	• 2/0 AWG • 4/0 AWG • 250 kcmil
Conductor - Copper Str Tap Range	2/0-250
Conductor - Copper Str Tap	• 2/0 AWG

Configuration

Physical Attribute - Number of	1
Crimps Required	
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	52.3 mm
Dimension - Height inch	2.06 in
Dimension - Height fraction	2-3/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

General

Plated	Y
Trade Name	HYGROUND®
Die Index	997
UPC	781810085288
Type	Taps
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810085288
UPC 14 Digit GTIN	00781810085288

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9800
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)