



YGHC34C26TN Compression Grounding C-TAP Connector

By Burndy

Catalog # [YGHC34C26TN](#)

Cu Compression Ground Tap Connector, .88 IN L, 300-500 Kcmil (Run), # 6 Sol. To 2/0 str (Tap), Tin Plated



Features

- Irreversible compression ground tap figure C connector
- C-shaped opening permits placing two continuous parallel cables into conductor groove
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • IEEE 837 • UL468A-468B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	Direct Burial
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Rod Run Range	3/4 in
Conductor - Rod Run	3/4 in
Conductor - Copper Str Run Range	300 kcmil-500 kcmil
Conductor - Copper Str Run	• 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor - Copper Solid Tap Range	6 AWG-3/0 AWG
Conductor - Copper Solid Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG

Conductor - Copper Str Tap Range 7 AWG-2/0 AWG

- Conductor - Copper Str Tap
- 7 AWG
 - 6 AWG
 - 5 AWG
 - 4 AWG
 - 3 AWG
 - 2 AWG
 - 1 AWG
 - 1/0
 - 2/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	61.5 mm
Dimension - Height inch	2.42 in
Dimension - Height fraction	2-21/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

General

Plated	Y
Trade Name	HYTAP™
Die Index	1011
UPC	781810327937
Type	Taps
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810327937
UPC 14 Digit GTIN	00781810327937

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5920
Carton Quantity	20



A Hubbell brand