



YGHC34C29TN Compression Grounding C-TAP Connector

By Burndy
Catalog # [YGHC34C29TN](#)

Cu Compression Ground Tap Connector, .88 IN L, 300-500 Kcmil (Run), 3/0 Str. - 250 Kcmil (Tap), Tin Plated

Features

- Irreversible compression ground tap figure C connector
- C-shaped opening permits placing two continuous parallel cables into conductor groove
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • IEEE 837 • UL468A-468B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	Direct Burial
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Run Range	300 kcmil-500 kcmil
Conductor - Copper Str Run	• 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor - Copper Str Tap Range	3/0-250
Conductor - Copper Str Tap	• 3/0 AWG • 4/0 AWG • 250 kcmil

Configuration

Physical Attribute - Number of	2
Crimps Required	
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	67.8 mm
Dimension - Height inch	2.67 in
Dimension - Height fraction	2-2/3 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.88 in

General

Plated	Y
Trade Name	HYTAP™
Die Index	1011
UPC	781810110867
Type	Taps
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810110867
UPC 14 Digit GTIN	00781810110867

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2960
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)