



YGHC34C34TN Compression Grounding C-TAP Connector

By Burndy
Catalog # [YGHC34C34TN](#)



Cu Compression Ground Tap Connector, 1.10 IN L, 300-500 Kcmil (Run), 300-500 Kcmil (Tap), Tin Plated

Features

- Irreversible compression ground tap figure C connector
- C-shaped opening permits placing two continuous parallel cables into conductor groove
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • IEEE 837 • UL468A-468B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	Direct Burial
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	300-500
Conductor - Copper Str Run	• 300 • 350 • 400 • 450 • 500
Conductor - Copper Str Tap Range	300-500
Conductor - Copper Str Tap	• 300 • 350 • 400 • 450 • 500

Configuration

Physical Attribute - Number of Crimps Required	3
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	73.9 mm
Dimension - Height inch	2.91 in
Dimension - Height fraction	2-81/89 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	28 mm
Dimension - Length Overall inch	1.10 in

General

Plated	Y
Trade Name	HYTAP™
Die Index	1011
UPC	781810110874
Type	Taps
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810110874
UPC 14 Digit GTIN	00781810110874

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2960
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)