



YGHHC26C26 Compression Grounding C-TAP Connector

By Burndy
Catalog # [YGHHC26C26](#)

HYTAP™ Connector, Compression Ground, Cable Range: 1 STR - 2/0 STR (RUN), 1 STR - 2/0 STR (TAP), Height: 1.54 in, Length: 0.75 in, Z: 1.88 in

Features

- Double Figure C Connector, C-Shaped opening permits two continuous parallel cables into conductor groove
- Qualified to IEEE-837 2014
- Prefilled with PENETROX compound and strip sealed

Application

Cable to Cable or Cable to Ground Rod Applications

General

Catalog Number	YGHHC26C26
Connector Type	Tap
Construction Material - Main	Copper
Die Index	O
EU RoHS Indicator	Contact Manufacturer
Material	Copper
Plated	N
Sub Brand	Connector
Trade Name	HYTAP™
Type	Taps
UPC	621945456228
UPC 14 Digit GTIN	00621945456228

Dimensions

Dimension - Height inch	1.54
Dimension - Height mm	0 mm
Dimension - Width inch	1.88
Height	1.54 in
Width	1.88 in

Conductor Related

Conductor - Copper Str Run Range	1 Stranded - 2/0 Stranded
----------------------------------	---------------------------

Conductor - Copper Str Tap Range	1 Stranded - 2/0 Stranded
Conductor - Rod Run Range	3/8" Rod
Conductor - Rod Size Range	3/8" Rod
Conductor - Rod Tap Range	3/8" Rod

Certifications And Compliance

Buy America(n) Qualified	BABA Compliant (All status valid till December 2024)
Certification - CSA Approved	[Delete]
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL 467 • IEEE 837 • IEEE 837 2014 Qualified • UL 486A-486B
Standards - Industry Standards Met	UL467;IEEE 837;IEEE 837 2014 Qualified;UL 486A-486B
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	30
Minimum Pack Quantity	1
Pallet Quantity	7200

Product Assets

- [Catalogs - Burndy Grounding Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50064429](#)
- [Specifications - YGHHC26C26](#)