



YGHHC29C29 Compression Grounding C-TAP Connector

By Burndy
Catalog # [YGHHC29C29](#)

Compression ground connector, Material: Copper, Range Run: 3/0 Str-250 Kcmil, 1/2" or 5/8" Rod; Tap: 3/0 Str-250 Kcmil.

Features

- Double Figure C Connector, C-Shaped opening permits two continuous parallel cables into conductor groove
- Qualified to IEEE-837 2014
- Prefilled with PENETROX compound and strip sealed

Application

For Direct Burial cables

Specifications

Standards - Industry Standards Met	• UL467 • IEEE 837 • IEEE 837 2014 Qualified • UL 486A-486B
Standards - RoHS Compliance Status	CM
Buy American Compliant	No
EU RoHS Indicator	Contact Manufacturer
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	• UL 467 • IEEE 837 • IEEE 837 2014 Qualified • UL 486A-486B
Certification - CSA Approved	[Delete]

Conductor

Conductor - Rod Run Range	• 1/2" • 5/8"
Conductor - Copper Str Run Range	3/0 Stranded - 250 kcmil

Conductor - Copper Str Tap Range	3/0 Stranded - 250 kcmil
----------------------------------	--------------------------

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
Trade Name	HYTAP™
Sub Brand	HYTAP
Die Index	997
UPC	621945456242
Type	Taps
Material	Copper
UPC 12 Digit	621945456242
UPC 14 Digit GTIN	00621945456242

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3840
Carton Quantity	40

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)