



YGHHC34C26 Compression Grounding C-TAP Connector

By Burndy
Catalog # [YGHHC34C26](#)

Compression ground connector, Material: Copper, Range Run: 300 Kcmil-500 Kcmil or 3/4" Rod, Tap: 6 SOL-2/0 STR

Features

- Double Figure C Connector, C-Shaped opening permits two continuous parallel cables into conductor groove
- Qualified to IEEE-837 2014
- Prefilled with PENETROX compound and strip sealed

Application

Cable to Cable or Cable to Ground Rod Applications

General

Catalog Number	YGHHC34C26
Connector Type	Tap
Construction Material - Main	Copper
Die Index	1011
EU RoHS Indicator	Contact Manufacturer
Material	Copper
Plated	N
Sub Brand	Connector
Trade Name	HYTAP™
Type	Taps
UPC	621945456259
UPC 14 Digit GTIN	00621945456259

Dimensions

Dimension - Height mm	0 mm
Width	2.13 in

Conductor Related

Conductor - Copper Solid Tap Range	6 Solid - 2/0 Solid
Conductor - Copper Str Run Range	300 - 500 kcmil

Conductor - Copper Str Tap Range	6 Stranded - 2/0 Stranded
Conductor - Rod Run Range	3/4" Rod

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Certification - CSA Approved	[Delete]
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL 467 • IEEE 837 • IEEE 837 2014 Qualified • UL 486A-486B
Standards - Industry Standards Met	UL467;IEEE 837;IEEE 837 2014 Qualified;UL 486A-486B
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	2400

Product Assets

- [Catalogs - Burndy Grounding Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section E1 - Compression Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50064429](#)
- [Specifications - YGHHC34C26](#)