

YGHP29C26TN Fig. 6 Cu Wire/Rod/Rebar Run to Cu Wire Tap, Tin

By Burndy

Catalog # [YGHP29C26TN](#)

HYTAP™ Figure 6 Tap HYGROUND® Compression Grounding Connector, 1/0 Str-250 kcmil, 1/2"-5/8" Rod, 3/8"-1/2" Rebar Run, 1/0-2/0 Str Tap

Features


- Irreversible compression ground tap can be used as a tap connector or as a tap splice connector
- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	Direct Burial
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Rebar Run Range	3 -4
Conductor - Rebar Run	• 3 • 4
Conductor - Rod Run Range	1/2 in-5/8 in
Conductor - Rod Run	• 1/2 in • 5/8 in
Conductor - Copper Str Run Range	1/0 -250 kcmil
Conductor - Copper Str Run	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - Copper Str Tap Range	1/0-2/0



Conductor - Copper Str Tap	• 1/0 • 2/0 AWG
----------------------------	---

Configuration

Physical Attribute - Number of Crimps Required	1
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.75 in
Dimension - Length Overall inch	2.09 in

General

Plated	Y
Trade Name	HYTAP™
Die Index	997
UPC	781810171530
Type	Taps
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810171530
UPC 14 Digit GTIN	00781810171530

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7350
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)