

YGHP29C6W6W Fig. 6, Cu 1/2"-5/8" Rod Run, #8 Sol-#6 Str Tap

By Burndy

Catalog # [YGHP29C6W6W](#)

High Strength Copper Irreversible Compression- Cable to cable, Cable to ground rod, Cable to rebar, 1/2"-5/8" Rod Run, #8 Sol-#6 Str Tap

Features

- Irreversible compression ground tap figure 6 can be used as a tap connector or as a tap splice connector
- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ compound and strip sealed

Application

For Direct Burial In Earth And Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rebar Run Range	3 -4
Conductor - Rebar Run	• 3 • 4
Conductor - Rod Size Range	1/2 in-5/8 in
Conductor - Rod Size	• 1/2 in • 5/8 in
Conductor - Copper Str Run Range	1/0 -250 kcmil
Conductor - Copper Str Run	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - Copper Solid Tap Range	8 AWG-5 AWG
Conductor - Copper Solid Tap	• 8 AWG • 7 AWG • 6 AWG • 5 AWG



Conductor - Copper Str Tap Range	8 AWG-5 AWG
Conductor - Copper Str Tap	• 8 AWG • 7 AWG • 6 AWG • 5 AWG

Configuration

Physical Attribute - Number of	1
Crimps Required	
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in

General

Trade Name	HYTAP™
Die Index	997
Oxide Inhibitor Type	Penetrox E
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYTAP
Product Type	Compression
UPC	781810085295
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810085295
UPC 14 Digit GTIN	00781810085295

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)