

YGHP2C2 Fig. 6, Cu #6 Sol-#2 Str Run and Tap

By Burndy
Catalog # [YGHP2C2](#)

High Strength Copper Irreversible Compression Ground Rod Tap
Connector

Features

- Irreversible compression ground tap can be used as a tap connector or as a tap splice connector
- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ compound and strip sealed

Application

For Direct Burial In Earth And Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	Direct Burial
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • IEEE 837 • IEEE 837 2014 Qualified
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Run Range	6-2
Conductor - Copper Str Run	• 6 • 5 • 4 • 3 • 2
Conductor - Copper Solid Run Range	6
Conductor - Copper Solid Run	6
Conductor - Copper Solid Tap Range	6
Conductor - Copper Solid Tap	6
Conductor - Copper Str Tap Range	6-2



Conductor - Copper Str Tap	• 6 • 5 • 4 • 3 • 2
----------------------------	---

Configuration

Physical Attribute - Number of Crimps Required	1
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in

General

Trade Name	HYTAP™
Die Index	O
Oxide Inhibitor Type	Penetrox E
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYTAP
Product Type	Compression
UPC	781810220917
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220917
UPC 14 Digit GTIN	00781810220917

Logistics

Minimum Pack Quantity	1
Pallet Quantity	17400
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)