



YGHP2C2TN Fig. 6 Ground Conn, #6 Sol- #2 Str Run/Tap, Tinned

By Burndy

Catalog # [YGHP2C2TN](#)

HYTAP™ Figure 6 Tap HYGROUND® Compression Connector or
Tap Splice Connector



Features

- Irreversible compression ground tap can be used as a tap connector or as a tap splice connector
- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	Direct Burial
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Run Range	7 AWG-2 AWG
Conductor - Copper Str Run	• 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Solid Run Range	6 AWG-1 AWG
Conductor - Copper Solid Run	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - Copper Solid Tap Range	6 AWG-1 AWG
Conductor - Copper Solid Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Conductor - Copper Str Tap Range	• 1 AWG 7-2
Conductor - Copper Str Tap	• 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.75 in
Dimension - Length Overall	1.40 in
inch	

General

Plated	Y
Trade Name	HYTAP™
Die Index	O
UPC	781810418888
Type	Taps
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810418888
UPC 14 Digit GTIN	00781810418888

Logistics

Minimum Pack Quantity	50
Pallet Quantity	17400
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)



A Hubbell brand