



YGHP34C29TN Fig. 6 Cu Wire/Rod/Rebar
Run to Cu Wire Tap, Tin

By Burndy
Catalog # [YGHP34C29TN](#)



HYTAP™ Figure 6 Tap HYGROUND® Compression Connector or
Tap Splice Connector

Features

- Irreversible compression ground tap can be used as a tap connector or as a tap splice connector
- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	Direct Burial
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Rebar Run Range	5 -6
Conductor - Rebar Run	• 5 • 6
Conductor - Rod Run Range	5/8 in-3/4 in
Conductor - Rod Run	• 5/8 in • 3/4 in
Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Run	• 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor - Copper Str Tap Range	3/0-250

Conductor - Copper Str Tap	• 3/0 AWG • 4/0 AWG • 250 kcmil
----------------------------	---

Configuration

Physical Attribute - Number of Crimps Required	1
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.75 in
Dimension - Length Overall inch	2.58 in

General

Plated	Y
Trade Name	HYTAP™
Die Index	998
UPC	781810203958
Type	Taps
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810203958
UPC 14 Digit GTIN	00781810203958

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5920
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)