



YGHP58C2W2TN Figure 6, 1/2"-5/8" Rod Run, #6-#2 Sol Tap, Tin

By Burndy
Catalog # [YGHP58C2W2TN](#)

Compression Ground Tap Connector, 1/2"-5/8" Rod Run, #6-#2 Sol Tap, Tin Plated

Features

- Tap A accepts a continuous run on tap conductor
- Tap B accepts a tap conductor only
- One connector style can be used for many applications reducing number of connectors needed in inventory
- High conductivity wrought copper extrusion, identical material to the conductor, minimizes resistance and voltage drop
- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	• UL467 • IEEE 837 • IEEE 837 2014 Qualified
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Solid Tap Range	#6 - #2 Solid
Conductor - Rod Tap Range	1/2" to 5/8"
Conductor Range	#6 AWG (Sol) - #2 AWG (Sol)

Dimensions

Dimension - Ground Rod Size	1/2 in - 5/8 in
Package Height	0.000 in
Package Weight	0.000 lb.
Dimension - Width mm	19.1 mm
Dimension - Width inch	0.75 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.90 in

General

Plated	Y
Die Index	997
UPC	781810058213
Type	Taps
Material	Copper
Plating Type	Tin Plated

Logistics

Minimum Pack Quantity	1
Pallet Quantity	8700
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)