



YGHR26C34TN Figure 8 Compression Ground Rod Connector

By Burndy
Catalog # [YGHR26C34TN](#)



HYTAIL™ Ground Rod Figure 8 Compression Tap Connector

Features

- High torque strength ground rod connector accepts a wide range of copper conductors to ground rod
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • IEEE 837
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Rod Size Range	3/4 in
Conductor Type	• CU C Str-Size A • Rod-Size B
Conductor - Copper Str Size Range	2 AWG - 2/O AWG
Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/O • 2/O AWG
Conductor - Rod Size	3/4 in

Configuration

Physical Attribute - Number of Crimps Required	1
--	---

Connector Type	Tap
----------------	-----

Dimensions

Dimension - Ground Rod Size	3/4
Package Height	0.000 in
Dimension - Height mm	55.6 mm
Dimension - Height inch	2.19 in
Dimension - Height fraction	2-15/79 in
Dimension - B Length fraction	22/25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	22 mm
Dimension - B Length inch	0.88 in
Dimension - Length Overall inch	0.88 in

General

Plated	Y
Trade Name	HYTAIL™
Die Index	• 998 • 1012
UPC	781810255193
Type	Taps
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810255193
UPC 14 Digit GTIN	00781810255193

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4640
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)