



YGHR26C58 Figure 8 Compression Ground Rod Connector

By Burndy
Catalog # [YGHR26C58](#)



HYTAIL™ Ground Rod Figure 8 Compression Tap Connector

Features

- High torque strength ground rod connector accepts a wide range of copper conductors to ground rod
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Application

For Direct Burial In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	• UL467 • IEEE 837
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Rod Size Range	5/8 in
Conductor - Copper Str Size	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG
Conductor - Rod Size	5/8 in
Conductor Type	• CU C Str-Size A • Rod-Size B
Conductor - Copper Str Size Range	2 AWG - 2/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
--	---

Connector Type

Tap

Dimensions

Dimension - Ground Rod Size	5/8
Package Height	0.000 in
Dimension - Height mm	50 mm
Dimension - Height inch	1.97 in
Dimension - Height fraction	1-32/33 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	22 mm
Dimension - B Length fraction	22/25 in
Dimension - B Length inch	0.88 in
Dimension - Length Overall inch	0.88 in

General

Trade Name	HYTAIL™
Die Index	• 998 • 1012
Oxide Inhibitor Type	Penetrox E
Prefilled Oxide Inhibitor	Y
Precrimp Die	UPRECRIMP58
Plated	No
Sub Brand	HYGROUND, HYTAIL
Product Type	Compression
UPC	781810220719
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220719
UPC 14 Digit GTIN	00781810220719

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4640
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)