



YGHR4C34 Figure 8 Compression Ground Rod Connector

By Burndy
Catalog # [YGHR4C34](#)



HYTAIL™ Ground Rod Figure 8 Compression Tap Connector

Features

- High torque strength ground rod connector accepts a wide range of copper conductors to ground rod
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • IEEE 837
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Str-Size A • Rod-Size B
----------------	--

Configuration

Connector Type	Tap
Dimensions	
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
General	
Plated	N
Trade Name	HYTAIL™
UPC	781810423745
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810423745
UPC 14 Digit GTIN	00781810423745

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2960
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)