



YGHS26 Compression Grounding Splice, 2/0 AWG Cu

By Burndy
Catalog # [YGHS26](#)

HYGROUND® Grounding Irreversible Compression Splice



Features

- Irreversible compression ground splices specifically designed for grounding applications
- Each conductor element has an inspection probe hole and a center stop to ensure proper cable insertion
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Application

For Direct Burial In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	• UL467 • UL 486A-486B • IEEE 837
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • UL 486A-486B • IEEE 837
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
--	---

Connector Type	Splice
Dimensions	
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	48 mm
Dimension - Outside Diameter inch	0.71 in
Dimension - B Length fraction	5/6 in
Dimension - B Length inch	0.83 in
Dimension - Length Overall inch	1.89 in
General	
Product Family	Grounding and Bonding Connectors>"Hyground" Compression Grounding Connectors>Inline Splices
Trade Name	HYLINK™
Die Index	15
Plated	No
Sub Brand	HYLINK
Product Type	Compression
UPC	781810220467
Type	Splices
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220467
UPC 14 Digit GTIN	00781810220467
Logistics	
Minimum Pack Quantity	1
Pallet Quantity	9600
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)