



YGHS27 Compression Grounding Splice, 3/0 AWG Cu

By Burndy
Catalog # [YGHS27](#)

HYGROUND® Grounding Irreversible Compression Splice



Features

- Irreversible compression ground splices specifically designed for grounding applications
- Each conductor element has an inspection probe hole and a center stop to ensure proper cable insertion
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • UL 486A-486B • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • UL 486A-486B • IEEE 837
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size Range	3/0 AWG
Conductor - Copper Str Size	3/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
--	---

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-1/6 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	66 mm
Dimension - B Length inch	1.18 in
Dimension - Outside Diameter inch	0.79 in
Dimension - Length Overall inch	2.59 in

General

Plated	N
Trade Name	HYLINK™
Die Index	16
UPC	781810169223
Type	Splices
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810169223
UPC 14 Digit GTIN	00781810169223

Logistics

Minimum Pack Quantity	10
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)