



YGLR29C12 Compression Ground Rod Connector

By Burndy
Catalog # YGLR29C12



GRIDLOK™ Ground Rod to Grid Compression Connector

Features

- Ground grid connector for a range of copper cable to ground rod
- Provides high torque strength on ground rod
- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	Direct Burial
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Rebar Tap	• 3 • 4
Conductor - Rod Size B Range	1/2 in
Conductor - Rod Size B	1/2 in
Conductor - Copper Str Size A	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - Copper Str Size A Range	2 AWG-250 kcmil
Conductor Type	• CU C Str-Size • Rod-Size • CU Weld C Str-Size

Configuration

Physical Attribute - Number of Crimps Required	1
Connector Type	Tap

Dimensions

Dimension - Ground Rod Size	1/2
Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	64 mm
Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - D inch	0.31 in
Dimension - Length BB inch	0.88 in
Dimension - Length Overall inch	2.53 in

General

Trade Name	GRIDLOK™
Die Index	997
Die Index - Element A	997
Die Index - Element B	1011
Oxide Inhibitor Type	Penetrox E
Prefilled Oxide Inhibitor	Y
Precrimp Die	UPRECRIMP12
Plated	N
UPC	781810220801
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220801
UPC 14 Digit GTIN	00781810220801

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2400
Carton Quantity	10

Product Assets

Catalog [English]