

YGS25 Compression Grounding Splice, 1/0 AWG Cu

By Burndy
Catalog # [YGS25](#)

HYGROUND® Grounding Irreversible Compression Splice



Features

- Irreversible compression ground splices specifically designed for grounding applications
- Each conductor element has an inspection probe hole and a center stop to ensure proper cable insertion
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL 486A-486B • UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Solid Size	1/0
Conductor - Copper Solid Size Range	1/0
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	1/0 Sol./Str.
Conductor - Copper Str Size	1/0 Sol./Str.

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Splice

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-1/3 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	75 mm
Dimension - B Length inch	1.35 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Length Overall inch	2.97 in

General

Plated	N
Trade Name	HYLINK™
Die Index	12
UPC	781810220603
Type	Splices
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220603
UPC 14 Digit GTIN	00781810220603

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9600
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)