



# YGS26 Compression Grounding Splice, 2/0 AWG Cu

By Burndy  
Catalog # [YGS26](#)

HYGROUND® Grounding Irreversible Compression Splice



## Features

- Irreversible compression ground splices specifically designed for grounding applications
- Each conductor element has an inspection probe hole and a center stop to ensure proper cable insertion
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

## Application

For Direct Burial In Earth Or Concrete

## Specifications

|                                         |                                                                                |
|-----------------------------------------|--------------------------------------------------------------------------------|
| Certification - UL Recognized           | No                                                                             |
| Buy American Compliant                  | No                                                                             |
| Certification - cULus                   | No                                                                             |
| Industry Standard(s)                    | <ul style="list-style-type: none"><li>• UL467</li><li>• UL 486A-486B</li></ul> |
| Certification - ETL                     | No                                                                             |
| Standards - Industry Standards Met      | <ul style="list-style-type: none"><li>• UL 486A-486B</li><li>• UL467</li></ul> |
| Standards - RoHS Compliance             | EX                                                                             |
| Status                                  |                                                                                |
| Certification - UL Listed Direct Burial | Yes                                                                            |
| UL Listed                               | Yes                                                                            |
| Certification - CSA Approved            | Yes                                                                            |

## Conductor

|                                   |               |
|-----------------------------------|---------------|
| Conductor - Copper Str Size       | 2/0 Str.      |
| Conductor Type                    | CU C Str-Size |
| Conductor - Copper Str Size Range | 2/0 Str.      |

## Configuration

|                                |        |
|--------------------------------|--------|
| Physical Attribute - Number of | 2      |
| Crimps Required                |        |
| Connector Type                 | Splice |

## Dimensions

|                                   |            |
|-----------------------------------|------------|
| Package Height                    | 0.000 in   |
| Package Weight                    | 0.000 lb.  |
| Package Length                    | 0.000 in   |
| Package Width                     | 0.000 in   |
| Dimension - L Length Overall mm   | 80 mm      |
| Dimension - Outside Diameter inch | 0.56 in    |
| Physical Attribute - Tongue Angle | Straight   |
| Dimension - B Length fraction     | 1-10/27 in |
| Dimension - B Length inch         | 1.45 in    |
| Dimension - Length Overall inch   | 3.13 in    |

## General

|                              |                                                                                                      |
|------------------------------|------------------------------------------------------------------------------------------------------|
| Product Family               | Grounding and Bonding<br>Connectors>"Hyground"<br>Compression Grounding<br>Connectors>Inline Splices |
| Trade Name                   | HYLINK™                                                                                              |
| Die Index                    | 13                                                                                                   |
| Plated                       | No                                                                                                   |
| Sub Brand                    | HYLINK                                                                                               |
| Product Type                 | Compression                                                                                          |
| UPC                          | 781810220412                                                                                         |
| Type                         | YGS, Grounding Irreversible                                                                          |
| Construction Material - Main | Copper                                                                                               |
| Material                     | Copper                                                                                               |
| Plating Type                 | Unplated                                                                                             |
| UPC 12 Digit                 | 781810220412                                                                                         |
| UPC 14 Digit GTIN            | 00781810220412                                                                                       |

## Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 9600 |
| Carton Quantity       | 10   |

## Product Assets

[Catalog \[English\]](#)