



YGS28 Compression Grounding Splice, 4/0 AWG Cu

By Burndy
Catalog # YGS28

HYGROUND® Grounding Irreversible Compression Splice



Features

- Irreversible compression ground splices specifically designed for grounding applications
- Each conductor element has an inspection probe hole and a center stop to ensure proper cable insertion
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Application

For Direct Burial In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	• UL467 • UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	• UL 486A-486B • UL467
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	4/0 Str.
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	4/0 Str.

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	86 mm
Dimension - Outside Diameter inch	0.69 in
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-7/20 in
Dimension - B Length inch	1.57 in
Dimension - Length Overall inch	3.37 in

General

Product Family	Grounding and Bonding Connectors>"Hyground" Compression Grounding Connectors>Inline Splices
Trade Name	HYLINK™
Die Index	15
Plated	No
Sub Brand	HYLINK
Product Type	Compression
UPC	781810220429
Type	Splices
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220429
UPC 14 Digit GTIN	00781810220429

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9600
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)