



YGS2C Compression Grounding Splice, 2 AWG Cu

By Burndy
Catalog # [YGS2C](#)

HYGROUND® Grounding Irreversible Compression Splice



Features

- Irreversible compression ground splices specifically designed for grounding applications
- Each conductor element has an inspection probe hole and a center stop to ensure proper cable insertion
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL 486A-486B • UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Solid Size	2
Conductor - Copper Solid Size Range	
Conductor Type	CU C Str-Size
Conductor - Copper Str Size	2 Sol./Str.
Conductor - Copper Str Size Range	
Conductor - Copper Str Size	2 Sol./Str.

Configuration

Physical Attribute - Number of Crimps Required	2
--	---

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	68 mm
Dimension - B Length inch	1.22 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Length Overall inch	2.67 in

General

Plated	N
Color Code	Brown
Trade Name	HYLINK™
Die Index	10
UPC	781810220405
Type	Splices
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220405
UPC 14 Digit GTIN	00781810220405

Logistics

Minimum Pack Quantity	1
Pallet Quantity	11600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)