



YH298CWC, Compression H-Tap

By Burndy
Catalog # [YH298CWC](#)

Copper Compression H Tap, 250 kcmil-2 AWG (Main), 8 AWG-14 AWG (Tap), Tin Plated

Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Tap Range	8 AWG
Conductor - Copper Flex K Tap	• 14 • 8
Conductor - Copper Flex M Run	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor - Copper Flex I Tap Range	8 AWG-14 AWG
Conductor - Copper Flex I Tap	• 14 • 8



Conductor - Copper Flex K Run	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor - Copper Flex G Run	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor - Copper Str Run Range	250 KCMIL-2 AWG
Conductor - Copper Flex G Tap Range	8 AWG-14 AWG
Conductor - Copper Str Run	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Flex G Tap	• 14 • 8
Conductor - Copper Flex M Tap	• 14 • 8
Conductor - Copper Flex H Tap Range	8 AWG-14 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	• 14 • 8
Conductor - Copper Flex I Run	4/0 AWG-2 AWG
Conductor - Copper Str Tap Range	8 AWG-14 AWG
Conductor - Copper Str Tap	• 14 • 12 • 10 • 9 • 8

Configuration

Connector Type	H-TAP W/BLK COVER
----------------	-------------------

Current

Voltage Rating	35 kV
----------------	-------

Voltage - Maximum	35000	Sub Brand	CRIMPIT
		UPC	781810000304
Dimensions		Type	Compression Taps
Package Height	0.000 in	Material	Copper
Package Weight	0.000 lb.	Plating Type	Tin - Electro Plated
Package Length	0.000 in	Finish Type	Tin-Plated
Package Width	0.000 in	UPC 12 Digit	781810000304
Dimension - L Length Overall	23 mm	UPC 14 Digit GTIN	00781810000304
mm			
Dimension - Strip Length inch	1-1/16	Logistics	
Dimension - Width inch	1.52 in	Minimum Pack Quantity	1
Dimension - Length Overall	0.90 in	Pallet Quantity	2250
inch		Carton Quantity	25
		Operational	
General		Temperature Rating	194
Trade Name	CRIMPIT™		
Die Index	654		
Plated	Y	Product Assets	
Color Code	Purple	Catalog [English]	



A Hubbell brand