



YH3434WCC, Compression H-Tap, Main 500-250 kcmil, Tap 500-250 kcmil, includes clear cover

By Burndy

Catalog # [YH3434WCC](#)

Copper Compression H Tap, 500 KCMIL-250 KCMIL (Main), 500 KCMIL-4/0 AWG(Tap), Tin Plated

Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	Yes
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	• Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Tap	• 4/0 • 250 • 300 • 350
Conductor - Copper Flex M Run	• 4/0 • 250 • 300 • 350



Conductor - Copper Flex I Tap Range	350 KCMIL-4/0 AWG
Conductor - Copper Flex I Tap	• 4/0 • 250 • 300 • 350
Conductor - Copper Flex K Run	• 4/0 • 250 • 300 • 350
Conductor - Copper Flex G Run	• 4/0 • 250 • 300 • 350
Conductor - Copper Str Run Range	500 KCMIL-250 KCMIL
Conductor - Copper Str Run	• 250 • 300 • 350 • 400 • 450 • 500
Conductor - Copper Flex G Tap	• 4/0 • 250 • 300 • 350
Conductor - Copper Flex M Tap	• 4/0 • 250 • 300 • 350
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	• 4/0 • 250 • 300 • 350
Conductor - Copper Flex I Run	350 KCMIL-4/0 AWG
Conductor - Copper Str Tap Range	500 KCMIL-4/0 AWG
Conductor - Copper Str Tap	• 4/0 • 250 • 300 • 350 • 400 • 450 • 500

Configuration

Connector TypeH-TAP W/CLR COVER

Current

Voltage Rating35 kV
Voltage - Maximum35000

Dimensions

Package Height0.000 in
Package Weight0.000 lb.
Package Length0.000 in
Package Width0.000 in
Dimension - L Length Overall25 mm
mm
Dimension - Strip Length inch1-1/8
Dimension - Width inch2.43 in
Dimension - Length Overall1.00 in
inch

General

Trade NameCRIMPIT™



A Hubbell brand

Die Index1104
PlatedY
Color CodeBrown
Sub BrandCRIMPIT
UPC781810436479
TypeCompression Taps
MaterialCopper
Plating TypeTin - Electro Plated
Finish TypeTin-Plated
UPC 12 Digit781810436479
UPC 14 Digit GTIN00781810436479

Logistics

Minimum Pack Quantity1
Pallet Quantity900
Carton Quantity10

Operational

Temperature Rating194

Product Assets

[Catalog \[English\]](#)