



YH3931WC, Compression H-Tap

By Burndy
Catalog # [YH3931WC](#)

Copper Compression H Tap, 750 KCMIL-350 KCMIL (Main), 4/0 AWG-1/0 AWG (Tap), Tin Plated



Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Tap Range	4/0 AWG
Conductor - Copper Flex K Tap	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Flex M Run	500
Conductor - Copper Flex I Tap Range	250 KCMIL-1/0 AWG
Conductor - Copper Flex I Tap	• 1/0 • 2/0 • 3/0 • 4/0

Conductor - Copper Flex K Run	• 250
Conductor - Copper Flex G Run	500
Conductor - Copper Str Run Range	750 KCMIL-350 KCMIL
Conductor - Copper Str Run	• 350 • 400 • 450 • 500 • 550 • 600 • 700
Conductor - Copper Flex G Tap	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Flex M Tap	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Flex I Run	550 KCMIL-500 KCMIL
Conductor - Copper Str Tap Range	4/0 AWG-1/0 AWG
Conductor - Copper Str Tap	• 1/0 • 2/0 • 3/0 • 4/0

Configuration

Connector Type	H-TAP W/BLK COVER
----------------	-------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length 0.000 in
Package Width 0.000 in
Dimension - L Length Overall 24 mm
mm
Dimension - Strip Length inch 1-1/16
Dimension - Width inch 2.97 in
Dimension - Length Overall 0.95 in
inch

General

Trade Name CRIMPIT™
Die Index KR
Plated Y
Color Code Yellow
Sub Brand CRIMPIT
UPC 781810000328
Type Compression Taps

Material Copper
Plating Type Tin - Electro Plated
Finish Type Tin-Plated
UPC 12 Digit 781810000328
UPC 14 Digit GTIN 00781810000328

Logistics

Minimum Pack Quantity 1
Pallet Quantity 720
Carton Quantity 5

Operational

Temperature Rating 194

Product Assets

[Catalog \[English\]](#)



A Hubbell brand