



YH3931WCC, Compression H-Tap, Main
750-350 kcmil, Tap 4/0-1/0 AWG, includes
clear cover

By Burndy
Catalog # [YH3931WCC](#)

Copper Compression H Tap, 750 KCMIL-350 KCMIL (Main), 4/0
AWG-1/0 AWG (Tap), Tin Plated

Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Tap Range	4/0 AWG
Conductor - Copper Flex K Tap	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Flex M Run	500
Conductor - Copper Flex I Tap Range	250 KCMIL-1/0 AWG
Conductor - Copper Flex I Tap	• 1/0



	• 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Flex K Run	500
Conductor - Copper Flex G Run	500
Conductor - Copper Str Run Range	750 KCMIL-350 KCMIL
Conductor - Copper Str Run	• 350 • 400 • 450 • 500 • 550 • 600 • 700
Conductor - Copper Flex G Tap	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Flex M Tap	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	• 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Flex I Run	550 KCMIL-500 KCMIL
Conductor - Copper Str Tap Range	4/0 AWG-1/0 AWG
Conductor - Copper Str Tap	• 1/0 • 2/0 • 3/0 • 4/0

Configuration

Connector Type	H-TAP W/CLR COVER
----------------	-------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	24 mm
mm	
Dimension - Strip Length inch	1-1/16
Dimension - Width inch	2.97 in
Dimension - Length Overall	0.95 in
inch	

General

Trade Name	CRIMPIT™
Die Index	KR
Plated	Y
Color Code	Yellow
Sub Brand	CRIMPIT



A Hubbell brand

UPC	781810436486
Type	Compression Taps
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810436486
UPC 14 Digit GTIN	00781810436486

Logistics

Minimum Pack Quantity	1
Pallet Quantity	450
Carton Quantity	5

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)