



YH4429WC, Compression H-Tap

By Burndy
Catalog # [YH4429WC](#)

Copper Compression H Tap, 1000 KCMIL-750 KCMIL (Main), 250 KCMIL-2 AWG (Tap), Tin Plated



Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

Application

Wire Tap

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Flex G Run	• 500 • 600 • 700
Conductor - Copper Str Run Range	1000 KCMIL-750 KCMIL
Conductor - Copper Str Run	• 700 • 750 • 800 • 850 • 900 • 1000
Conductor - Copper Flex G Tap	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0

Conductor - Copper Flex M Tap	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor - Material	COPPER
Conductor - Copper Flex K Tap	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor - Copper Flex M Run	• 500 • 600 • 700
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor - Copper Flex I Run	750 KCMIL-500 KCMIL
Conductor - Copper Str Tap Range	250 KCMIL-2 AWG
Conductor - Copper Str Tap	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250
Conductor - Copper Flex I Tap Range	4/0 AWG-2 AWG
Conductor - Copper Flex I Tap	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor - Copper Flex K Run	• 500 • 600 • 700

Configuration

Connector Type	H-TAP W/BLK COVER	Trade Name	CRIMPIT™	
Current		Die Index	KR	
		UPC	781810051054	
Voltage Rating	35 kV	Type	Compression Taps	
Voltage - Maximum	35000	Material	Copper	
Dimensions		Plating Type	Tin - Electro Plated	
		Finish Type	Tin-Plated	
		UPC 12 Digit	781810051054	
		UPC 14 Digit GTIN	00781810051054	
		Logistics		
Operational		Minimum Pack Quantity	1	
		Pallet Quantity	720	
		Carton Quantity	5	
General		Product Assets	Catalog [English]	
Plated	Y			
Color Code	Yellow			



A Hubbell brand