



YH4429WCC, Cu Compression H Tap and Clear Cover, 1000-750 kcmil Run, 250 kcmil-2 AWG Tap

By Burndy

Catalog # [YH4429WCC](#)

Copper Compression H Tap, 1000 KCMIL-750 KCMIL (Main), 250 KCMIL-2 AWG (Tap), Tin Plated

Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Tap	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor - Copper Flex M Run	• 500 • 600 • 700
Conductor - Copper Flex I Tap Range	4/0 AWG-2 AWG



Conductor - Copper Flex I Tap	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor - Copper Flex K Run	• 500 • 600 • 700
Conductor - Copper Flex G Run	• 500 • 600 • 700
Conductor - Copper Str Run Range	1000 KCMIL-750 KCMIL
Conductor - Copper Str Run	• 700 • 750 • 800 • 850 • 900 • 1000
Conductor - Copper Flex G Tap	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor - Copper Flex M Tap	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	• 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0
Conductor - Copper Flex I Run	750 KCMIL-500 KCMIL
Conductor - Copper Str Tap Range	250 KCMIL-2 AWG
Conductor - Copper Str Tap	• 2 • 1 • 1/0 • 2/0

- 3/0
- 4/0
- 250

Configuration

Connector TypeH-TAP W/CLR COVER

Current

Voltage Rating35 kV
Voltage - Maximum35000

Dimensions

Package Height0.000 in
Package Weight0.000 lb.
Package Length0.000 in
Package Width0.000 in
Dimension - L Length Overall25 mm
mm
Dimension - Strip Length inch1-3/8
Dimension - Width inch3.32 in
Dimension - Length Overall1.00 in
inch

General



Trade NameCRIMPIT™
Die IndexKR
PlatedY
Color CodeYellow
Sub BrandCRIMPIT
UPC781810436509
TypeCompression Taps
MaterialCopper
Plating TypeTin - Electro Plated
Finish TypeTin-Plated
UPC 12 Digit781810436509
UPC 14 Digit GTIN00781810436509

Logistics

Minimum Pack Quantity1
Pallet Quantity450
Carton Quantity5

Operational

Temperature Rating194

Product Assets

[Catalog \[English\]](#)