



YH4444WC, Compression H-Tap

By Burndy
Catalog # [YH4444WC](#)

Copper Compression H Tap, 1000 KCMIL-750 KCMIL (Main), 1000 KCMIL-750 KCMIL (Tap), Tin Plated



Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Tap	• 500 • 600 • 700
Conductor - Copper Flex M Run	• 500 • 600 • 700
Conductor - Copper Flex I Tap Range	750 KCMIL-350 KCMIL
Conductor - Copper Flex I Tap	• 500 • 550 • 600 • 700
Conductor - Copper Flex K Run	• 500 • 600

Conductor - Copper Flex G Run	• 700 • 500 • 600 • 700
Conductor - Copper Str Run Range	1000 KCMIL-750 KCMIL
Conductor - Copper Str Run	• 700 • 750 • 800 • 850 • 900 • 1000
Conductor - Copper Flex G Tap	• 500 • 600 • 700
Conductor - Copper Flex M Tap	• 500 • 600 • 700
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	• 500 • 600 • 700
Conductor - Copper Flex I Run	750 KCMIL-500 KCMIL
Conductor - Copper Str Tap Range	1000 KCMIL-750 KCMIL
Conductor - Copper Str Tap	• 750 • 800 • 850 • 900 • 1000

Configuration

Connector Type	H-TAP W/BLK COVER
----------------	-------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	25 mm
Dimension - Strip Length inch	1-1/8

Dimension - Width inch	3.38 in	Finish Type	Tin-Plated
Dimension - Length Overall inch	1.00 in	UPC 12 Digit	781810000342
		UPC 14 Digit GTIN	00781810000342
General		Logistics	
Trade Name	CRIMPIT™	Minimum Pack Quantity	1
Die Index	1102	Pallet Quantity	720
Plated	Y	Carton Quantity	5
Color Code	White		
Sub Brand	CRIMPIT	Operational	
UPC	781810000342	Temperature Rating	194
Type	Compression Taps		
Material	Copper	Product Assets	
Plating Type	Tin - Electro Plated	Catalog [English]	



A Hubbell brand