



YH4444WCC, Compression H-Tap, Main 1000-750 kcmil, Tap 1000-750 kcmil, includes clear cover

By Burndy

Catalog # [YH4444WCC](#)

Copper Compression H Tap, 1000 KCMIL-750 KCMIL (Main), 1000 KCMIL-750 KCMIL (Tap), Tin Plated

Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Tap	• 500 • 600 • 700
Conductor - Copper Flex M Run	• 500 • 600 • 700
Conductor - Copper Flex I Tap Range	750 KCMIL-350 KCMIL
Conductor - Copper Flex I Tap	• 500 • 550 • 600 • 700



Conductor - Copper Flex K Run	• 500 • 600 • 700
Conductor - Copper Flex G Run	• 500 • 600 • 700
Conductor - Copper Str Run Range	1000 KCMIL-750 KCMIL
Conductor - Copper Str Run	• 700 • 750 • 800 • 850 • 900 • 1000
Conductor - Copper Flex G Tap	• 500 • 600 • 700
Conductor - Copper Flex M Tap	• 500 • 600 • 700
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	• 500 • 600 • 700
Conductor - Copper Flex I Run	750 KCMIL-500 KCMIL
Conductor - Copper Str Tap Range	1000 KCMIL-750 KCMIL
Conductor - Copper Str Tap	• 750 • 800 • 850 • 900 • 1000

Configuration

Connector Type	H-TAP W/CLR COVER
----------------	-------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall mm 25 mm
Dimension - Strip Length inch 1-1/8
Dimension - Width inch 3.38 in
Dimension - Length Overall inch 1.00 in

General

Trade Name CRIMPIT™
Die Index 1102
Plated Y
Color Code White
Sub Brand CRIMPIT
UPC 781810436516
Type Compression Taps
Material Copper

Plating Type Tin - Electro Plated
Finish Type Tin-Plated
UPC 12 Digit 781810436516
UPC 14 Digit GTIN 00781810436516

Logistics

Minimum Pack Quantity 1
Pallet Quantity 450
Carton Quantity 5

Operational

Temperature Rating 194

Product Assets

[Catalog \[English\]](#)



A Hubbell brand