



YH6C6CWC, Compression H-Tap

By Burndy
Catalog # [YH6C6CWC](#)

Copper compression H tap with black flame retardant cover



Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

Application

Wire Tap

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Run Range	6 AWG-10 AWG
Conductor - Material	COPPER
Conductor Type	CODE/FLEX
Conductor - Copper Flex I Run	6 AWG-10 AWG

Conductor - Copper Str Tap Range	6 AWG-14 AWG
Conductor - Copper Flex I Tap Range	6 AWG-14 AWG

Configuration

Connector Type	H-TAP W/CLR COVER
----------------	-------------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Color Code	Orange
Trade Name	CRIMPIT™
Sub Brand	CRIMPIT
Die Index	BG
UPC	781810051047
Type	Compression Taps
Material	Copper
Finish Type	Tin-Plated

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3300
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)