



YHD200, Compression Line Tap, CU, AL, ACSR, Compact

By Burndy
Catalog # [YHD200](#)



Compression Line Tap for Copper, AL or ACSR and Compact Conductors, wire diameter range, groove A(Run):0.398-0.470

Features

- Wide range, Universal and Reversible Figure H Shapped aluminum compression connector
- Bendable tabs secure both run and tap conductors freeing the installers hands to work with the installation tool
- Massive aluminum design minimizes corrosion due to galvanic corrosion
- Pre-filled with PENETROX Joint Compound and individually packaged
- Conductor ranges and tooling is clearly printed on connector and package

Application

For Copper, Aluminum Or ACSR And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	2/0 AWG-3/0 AWG
Conductor - ACSR Cmpt Run	• 2/0 AWG • 3/0 AWG
Conductor - AL Str Run Range	3/0 - 4/0
Conductor - AL Str Run	3/0 - 4/0
Conductor - AL Str Tap Range	6 AWG-1 AWG
Conductor - AL Str Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG-1 AWG
Conductor - ACSR Cmpt Tap	• 6 AWG • 4 AWG • 3 AWG

Conductor - ACSR Str Run Range	• 2 AWG • 1 AWG 1/0 (6/1) Raven AWG-2/0 (6/1) Quail AWG
Conductor - ACSR Str Run	• 1/0 (6/1) Raven AWG • 2/0 (6/1) Quail AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - ACSR Str Tap	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - Copper Str Run Range	2/0 AWG-3/0 AWG
Conductor - Copper Str Run	• 2/0 AWG • 3/0 AWG
Conductor - Copper Solid Run Range	3/0 AWG-4/0 AWG
Conductor - Copper Solid Run	• 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-1/0 AWG
Conductor - Copper Solid Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG
Conductor - Copper Str Tap Range	6 AWG-1 AWG
Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	36.8 mm
Dimension - Height inch	1.45 in
Dimension - Height fraction	1-11/25 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in	Product Type	Compression
Dimension - L Length Overall mm	41 mm	UPC	781810139158
Dimension - Width mm	23 mm	Type	YHD
Dimension - Width inch	0.89 in	Material	Aluminum
Dimension - Length Overall inch	1.62 in	Plating Type	Unplated
		UPC 14 Digit GTIN	00781810139158
General		Logistics	
Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>H-Taps	Minimum Pack Quantity	25
Trade Name	HYCRIMP™	Pallet Quantity	8250
Die Index	D3	Carton Quantity	250
Prefilled Oxide Inhibitor	Y	Product Assets	
Plated	No	Catalog [English]	
Sub Brand	HYCRIMP		

