



YHD200J1444, Stirrup

By Burndy
Catalog # [YHD200J1444](#)



HYCRIMP™ STIRRUP.

Features

- HYCRIMP STIRRUP

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - AL Str Size Range	2/0 AWG-4/0 AWG
Conductor - ACSR Str Size	• 1/0 (6/1) Raven AWG • 2/0 (6/1) Quail AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG-2/0 (6/1) Quail AWG

Configuration

Connector Type	H-Tap
----------------	-------

Dimensions

Dimension - Pad Width inch	5.00 in
----------------------------	---------

Dimension - Height mm	0 mm
Dimension - B Length fraction	1-22/25 in
Dimension - L Length Overall mm	305 mm
Dimension - B Length inch	1.88 in
Dimension - D inch	3.00 in
Dimension - Length Overall inch	12.0 in

General

Plated	Y
Trade Name	HYCRIMP™
Die Index	D3
UPC	781810054215
Type	Bail
Material	Aluminum
Material - Bail	Copper
Plating Type	Tin
UPC 12 Digit	781810054215
UPC 14 Digit GTIN	00781810054215

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1440
Carton Quantity	16

Product Assets

[Catalog \[English\]](#)