



YHD300, Line Tap, Cu, AL, ACSR, Compact

By Burndy

Catalog # [YHD300](#)

Compression Line Tap for Copper, AL or ACSR and Compact
Conductors, wire diameter range- groove A(Run): 0.336 - 0.470



Features

- Wide range, Universal and Reversible Figure H Shapped aluminum compression connector
- Bendable tabs secure both run and tap conductors freeing the installers hands to work with the installation tool
- Massive aluminum design minimizes corrosion due to galvanic corrosion
- Pre-filled with PENETROX Joint Compound and individually packaged
- Conductor ranges and tooling is clearly printed on connector and package

Application

For Copper, Aluminum Or ACSR And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Yes
Certification - cULus	No
Buy America(n) Qualified	• Buy America Compliant (All status valid till December 2026) • Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	1/0 AWG-2/0 AWG
Conductor - ACSR Cmpt Run	• 1/0 AWG • 2/0 AWG
Conductor - AL Str Run Range	2/0 - 4/0
Conductor - AL Str Run	2/0 - 4/0
Conductor - AL Str Tap Range	1 AWG-2/0 AWG
Conductor - AL Str Tap	• 1 AWG • 1/0 AWG • 2/0 AWG
Conductor - ACSR Cmpt Tap Range	1/0 AWG-3/0 AWG
Conductor - ACSR Cmpt Tap	• 1/0 AWG

Conductor - ACSR Str Run Range	• 2/0 AWG • 3/0 AWG 1 (6/1) Robin AWG-2/0 (6/1) Quail AWG
Conductor - ACSR Str Run	• 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG • 2/0 (6/1) Quail AWG
Conductor - ACSR Str Tap Range	1 (6/1) Raven AWG-2/0 (6/1) Quail AWG
Conductor - ACSR Str Tap	• 1 (6/1) Raven AWG • 2/0 (6/1) Quail AWG
Conductor - Copper Str Run Range	#1(3)-3/0
Conductor - Copper Str Run	• #1(3) • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0
Conductor - Copper Solid Run Range	2/0 AWG-4/0 AWG
Conductor - Copper Solid Run	• 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Tap Range	2/0 AWG-3/0 AWG
Conductor - Copper Solid Tap	• 2/0 AWG • 3/0 AWG
Conductor - Copper Str Tap Range	2/0 AWG-3/0 AWG
Conductor - Copper Str Tap	• 2/0 AWG • 3/0 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	36.1 mm
Dimension - Height inch	1.42 in
Dimension - Height fraction	1-21/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	41 mm
Dimension - Width fraction	89/100 in
Dimension - Width mm	23 mm
Dimension - Width inch	0.89 in
Dimension - Length Overall inch	1.62 in

General

Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>H-Taps	Material Plating Type UPC 14 Digit GTIN	Aluminum Unplated 00781810139257
Trade Name	HYCRIMP™	Logistics	
Die Index	D3	Minimum Pack Quantity	25
Prefilled Oxide Inhibitor	Y	Pallet Quantity	8250
Plated	No	Carton Quantity	250
Sub Brand	HYCRIMP	Product Assets	
Product Type	Compression	Catalog [English]	
UPC	781810139257		
Type	YHD		



A Hubbell brand