



YHD350, Line Tap Connector, AL-CU, AL-AL

By Burndy
Catalog # [YHD350](#)

Compression Line Tap for Copper, AL or ACSR and Compact Conductors, wire diameter range, groove A(Run):0.461-0.563



Features

- Wide range, Universal and Reversible Figure H Shapped aluminum compression connector
- Bendable tabs secure both run and tap conductors freeing the installers hands to work with the installation tool
- Massive aluminum design minimizes corrosion due to galvanic corrosion
- Pre-filled with PENETROX Joint Compound and individually packaged
- Conductor ranges and tooling is clearly printed on connector and package

Application

For Copper, Aluminum Or ACSR And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	1/0 AWG-2/0 AWG
Conductor - ACSR Cmpt Run	• 1/0 AWG • 2/0 AWG
Conductor - AL Str Run Range	3/0-4/0
Conductor - AL Str Run	3/0-4/0
Conductor - AL Str Tap Range	2/0 AWG-3/0 AWG
Conductor - AL Str Tap	• 2/0 AWG • 3/0 AWG
Conductor - ACSR Cmpt Tap Range	1 AWG-2/0 AWG
Conductor - ACSR Cmpt Tap	• 1 AWG • 1/0 AWG • 3/0 AWG • 2/0 AWG
Conductor - ACSR Str Run Range	3/0 (6/1) Pigeon AWG-4/0 (6/1) Penquin AWG

Conductor - ACSR Str Run	• 3/0 (6/1) Pigeon AWG • 4/0 (6/1) Penquin AWG
Conductor - ACSR Str Tap Range	1 (6/1) Robin AWG-2/0 (6/1) Quail AWG
Conductor - ACSR Str Tap	• 1 (6/1) Robin AWG • 1/0 (6/1) Raven AWG • 2/0 (6/1) Quail AWG
Conductor - Copper Str Run Range	3/0 AWG-4/0 AWG
Conductor - Copper Str Run	• 3/0 AWG • 4/0 AWG
Conductor - Copper Solid Run Range	250 - 300
Conductor - Copper Solid Run	250 - 300
Conductor - Copper Solid Tap Range	2/0 AWG-3/0 AWG
Conductor - Copper Solid Tap	• 2/0 AWG • 3/0 AWG
Conductor - Copper Str Tap Range	1 AWG-2/0 AWG
Conductor - Copper Str Tap	• 1 AWG • 1/0 • 2/0 AWG

Dimensions

Package Height	2.750 in
Dimension - Height mm	36.1 mm
Dimension - Height inch	1.42 in
Dimension - Height fraction	1-21/50 in
Package Weight	4.450 lb.
Package Length	13.300 in
Package Width	4.750 in
Dimension - L Length Overall mm	57 mm
Dimension - Width fraction	89/100 in
Dimension - Width mm	23 mm
Dimension - Width inch	0.89 in
Dimension - Length Overall inch	2.25 in

General

Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>H-Taps
Trade Name	HYCRIMP™
Die Index	D3
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYCRIMP
Product Type	Compression

UPC	781810139301	Minimum Pack Quantity	25
Type	YHD	Pallet Quantity	3200
Material	Aluminum	Carton Quantity	200
Plating Type	Unplated		
UPC 14 Digit GTIN	00781810139301		

Product Assets

[Catalog \[English\]](#)

Logistics



A Hubbell brand