



YHD350J1496, Stirrup

By Burndy
Catalog # [YHD350J1496](#)

HYCRIMP™ STIRRUP.

Features

- HYCRIMP STIRRUP

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil
Conductor - AL Str Size Range	3/0 AWG - 300 kcmil
Conductor - ACSR Str Size	• 3/0 (6/1) Pigeon AWG • 4/0 (6/1) Penguin AWG
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG-4/0 (6/1) Penguin AWG

Configuration

Connector Type	H-Tap
----------------	-------

Dimensions

Dimension - Pad Width inch	5.00 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	2-1/2 in
Dimension - L Length Overall mm	394 mm
Dimension - B Length inch	2.50 in
Dimension - D inch	4.75 in
Dimension - Length Overall inch	15.5 in

General

Plated	Y
Trade Name	HYCRIMP™
Die Index	D3
UPC	781810081167
Type	Bail
Material	Aluminum
Material - Bail	Copper
Plating Type	Tin
UPC 12 Digit	781810081167
UPC 14 Digit GTIN	00781810081167

Logistics

Minimum Pack Quantity	1
Pallet Quantity	768
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)