



YHN500J1496, Stirrup

By Burndy

Catalog # [YHN500J1496](#)

HYCRIMP™ STIRRUP.



Features

- HYCRIMP STIRRUP

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil
Conductor - AL Str Size Range	4/0 AWG-500 kcmil
Conductor - ACSR Str Size	• 4/0 (6/1) Penguin AWG • 80 (8/1) Grouse kcmil • 101.8 (12/7) Petrel kcmil • 110.8 (12/7) Minorca kcmil • 134.6 (12/7) Leghorn kcmil • 159 (12/7) Guinea kcmil • 176.9 (12/7) Dotterel kcmil • 190.8 (12/7) Dorking kcmil • 211.3 (12/7) Cochin kcmil • 203.2 (16/9) Brahma kcmil • 266.8 (18/1) Waxwing kcmil • 266.8 (26/7) Owl kcmil • 266.8 (26/7) Partridge kcmil • 300.0 (26/7) Ostrich kcmil • 336.4 (18/1) Merlin kcmil • 336.4 (26/7) Linnet kcmil • 336.4 (30/7) Oriole kcmil • 397.5 (18/1) Chickadee kcmil • 397.5 (24/7) Brant kcmil • 397.5 (26/7) Ibis kcmil

Conductor - ACSR Str Size Range	4/0 (6/1) Penguin AWG-477. (30/7) Hen kcmil
---------------------------------	---

Configuration

Connector Type	H-Tap
----------------	-------

Dimensions

Dimension - Pad Width inch	5.00 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	2/1 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	394 mm
Dimension - B Length inch	2.00 in
Dimension - D inch	4.75 in
Dimension - Length Overall inch	15.5 in

General


Plated	Y
Trade Name	HYCRIMP™
Die Index	N
UPC	781810081174
Type	Bail
Material	Aluminum
Material - Bail	Copper
Plating Type	Tin
UPC 12 Digit	781810081174
UPC 14 Digit GTIN	00781810081174

Logistics

Minimum Pack Quantity	1
Pallet Quantity	540
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)



- 397.5 (30/7) Larkspur kcmil
- 477.0 (18/1) Pelican kcmil
- 477.0 (24/7) Flicker kcmil
- 477.0 (26/7) Hawk kcmil
- 477. (30/7) Hen kcmil