



YHO1, H-shaped Aluminum Connector

By Burndy
Catalog # [YHO1](#)

Wide range taking H-style AL connector; prefilled with PENETROX™



Features

- LOKTAP™ compression connectors are high quality, range-taking devices accommodating many combinations of conductor
- LOKTAP™ connectors feature a C groove on both sides of the connector for use in street lighting applications

Application

For Copper, Aluminum Or ACSR And Compact Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Run Range	#6-#1
Conductor - ACSR Cmpt Run	• #6 • 4 AWG • 3 AWG • 2 AWG • #1
Conductor - AL Str Run Range	6 AWG-1 AWG
Conductor - AL Str Run	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - AL Str Tap Range	6 AWG-2 AWG
Conductor - AL Str Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG-1 AWG
Conductor - ACSR Cmpt Tap	• 6 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG

Conductor - ACSR Str Run Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - ACSR Str Run	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-2 (7/1) Sparate AWG
Conductor - ACSR Str Tap	• 6 (6/1) Turkey AWG • 5 (6/1) Thrush AWG • 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG • 3 (6/1) Swallow AWG • 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - Copper Str Run Range	6 AWG-1 AWG
Conductor - Copper Str Run	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - Copper Solid Run Range	6 AWG-1 AWG
Conductor - Copper Solid Run	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor - Copper Solid Tap Range	#6-#1
Conductor - Copper Solid Tap	• #6 • 5 AWG • 4 AWG • 3 AWG • 2 AWG • #1
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Dimensions

Package Height	0.000 in
Dimension - Height mm	28.2 mm
Dimension - Height inch	1.11 in
Dimension - Height fraction	1-11/100 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	32 mm
Dimension - Width fraction	67/100 in
Dimension - Width mm	17 mm
Dimension - Width inch	0.67 in
Dimension - Length Overall inch	1.25 in

General

Product Family	Utility Overhead & Underground Distribution>Compression Tap Connectors>H-Taps
----------------	---

Trade Name	LOKTAP™
Die Index	O
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	LOKTAP
Product Type	Compression
UPC	781810139011
Type	YHO
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810139011

Logistics

Minimum Pack Quantity	25
Pallet Quantity	11550
Carton Quantity	350

Product Assets

[Catalog \[English\]](#)



A Hubbell brand